


(F)17, (F)18, (F)19, (F)24, (F)25 Hinge Stile Preparation

Electrified Devices, Wood Door, LHR Shown, RHR Opposite

- 6" FOR FLUSH DOORS
- 1" LESS THAN STILE FOR STILED DOORS




CLEAR CHANNEL ACCESS REQUIRED FOR WIRE CONNECTION

CONDUCTING HINGE OR APPROVED POWER TRANSFER - SUPPLIED BY OTHERS

NOTE: FOR DELAYED EGRESS DEVICES, TRANSFER MUST BE U.L. APPROVED

"A" DIA. (TO BE PREPARED AT TIME OF DEVICE INSTALLATION)

DRILL 3/8" DIA. HOLE THRU FOR SEXBOLT (TO BE PREPARED AT TIME OF DEVICE INSTALLATION)



ELECTRIFICATION FEATURE	"A"
ELECTRIC LATCH RETRACTION (ELR)	1/2"
ELECTRIC DOGGING (ED)	1/2"
DELAYED EGRESS (DE - 18 SERIES ONLY)	3/4"
SECURITY MONITORING (AE, DM, LK, LM, SM)	1/2"
ELECTRIC LOCK/UNLOCK TRIM (FSA/FSE)	1/2"
HARD WIRE EXIT ALARM (HWEA)	1/2"

TEMPLATE
W-5020-b